


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0511030200**  
**Status:** **Active**  
**Description:** 2.50mm Pitch Wire-to-Wire and Wire-to-Board Housing, Positive Lock, 2 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51103-025 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51103-026 (PDF)</a>
<a href="#">Product Specification PS-51103-001 (PDF)</a>	<a href="#">Product Specification PS-51103-027 (PDF)</a>
<a href="#">Product Specification PS-51103-002 (PDF)</a>	<a href="#">Product Specification PS-51103-028 (PDF)</a>
<a href="#">Product Specification PS-51103-005 (PDF)</a>	<a href="#">Product Specification PS-51198-003 (PDF)</a>
<a href="#">Product Specification PS-51103-006 (PDF)</a>	<a href="#">Packaging Specification SPK-51103-001 (PDF)</a>
<a href="#">Product Specification PS-51103-024 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	51103
Application	Signal, Wire-to-Board, Wire-to-Wire
MolexKits	Yes
Product Name	N/A
UPC	800754316880

**Physical**

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	227.300/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-51103-001
Product Specification	PS-51103-001, PS-51103-002, PS-51103-005, PS-51103-006, PS-51103-024, PS-51103-025, PS-51103-026, PS-51103-027, PS-51103-028, PS-51198-003, RPS-51103-001, RPS-51103-002, RPS-51103-003, RPS-51103-009, RPS-51103-010, RPS-51103-011, RPS-51103-012, RPS-51103-017, RPS-51103-018, RPS-51103-021, RPS-51103-022, RPS-51103-027, RPS-51103-032, RPS-51103-033, RPS-51103-034, RPS-51103-039, RPS-51103-041, RPS-51103-043, RPS-51103-044, RPS-51103-046, RPS-51103-047, RPS-51103-049, RPS-51103-050, RPS-51103-051, RPS-51103-056, RPS-51103-057, RPS-51163-004, RPS-53375-001
Sales Drawing	SD-51103-020, SD-51103-021

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

51103 Series

**Mates With**

51198 , 53375 , 53426 , 53517 , 53608

**Use With**

50351 , 50752

This document was generated on 10/03/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**