

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008701039

Status:

Active

Overview:

SPOX™ BMI Connector System

Description:

2.50mm Pitch SPOX™ Wire-to-Board Crimp Terminal, Reel

Documents:

3D Model

Drawing (PDF)

Product Specification PS-5264-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Packaging Alternative

Product Name

UPC

Crimp Terminals

5263

Signal

Yes

SPOX™ BMI Connector System

08-70-1040 (Loose)

SPOX™

800753534902

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

Phosphor Bronze

Tin

Tin

43.200/mg

Reel

0.889µm

0.914µm

Crimp or Compression

1.90mm max.

22, 24, 26, 28

N/A

Material Info

Engineering Number

5263PBT

Reference - Drawing Numbers

Crimp Specification


Product Specification

CS-5263

PS-5264-001, RPS-5263-001, RPS-5264-002, RPS-5264-003, RPS-5264-004, RPS-5264-005, RPS-5264-006

SD-5263-003

Sales Drawing



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

5263 Series

Use With

5264

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for Crimp Terminals	0638115200
Manual Extraction Tool	0638131400
FineAdjust™ Applicator for	0639023100

2.50mm Pitch Crimp
Terminal
FineAdjust™ 0639026400
Applicator for
2.50mm (.098")
Pitch SPOX™ Crimp
Terminal
T2 Terminator for 0639123100
2.50mm Pitch Crimp
Terminal

Japan	
Description	Product #
Applicator for M211A Bench Press, 22-28 AWG Wire	<u>0011260117</u>

This document was generated on 09/19/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION