

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934445112](#)  
**Status:** **Active**  
**Overview:** ML-XT™ Sealed Connection System  
**Description:** ML-XT™ Sealed 8 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option A, Grey

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification 934430002 \(PDF\)](#)  
[Product Specification 934430010 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification 934430010 \(PDF\)](#)

**General**

Product Family Crimp Housings  
 Series [93444](#)  
 Application Power, Signal, Wire-to-Wire  
 Overview ML-XT™ Sealed Connection System  
 Product Name ML-XT™  
 UPC 889056392433

**Physical**

Circuits (maximum) 8  
 Color - Resin Grey  
 Gender Receptacle  
 Glow-Wire Compliant No  
 Keying to Mating Part Yes  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 15.610/g  
 Number of Rows 4  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface N/A  
 Polarized to Mating Part Yes  
 Temperature Range - Operating -55°C to +125°C

**Electrical**

Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**

Application Specification 934430010  
 Packaging Specification 934430002  
 Product Specification 934430010  
 Sales Drawing 934430050



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[93444 Series](#)

**Mates With**

ML-XT™ Sealed 8 Circuit Plug Housing [93445-5112](#)

**Use With**

ML-XT™ Male (Pin) Terminal [84524-0004](#) (Nickel), ML-XT™ Male (Pin) Terminal [84524-0014](#) (Selective Gold), ML-XT™ 8 Circuit Receptacle Wedgelock [93447](#) , ML-XT™ Blind Cavity Plug [93494-1000](#)