

## Cable housing - KGS-MSTB 2,5/16 - 1783850

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 16, Dimension a: 80 mm, Color: green

### Why buy this product

- Straight cable outlet for sequencing several cable housings
- Easier plug-in and disconnection processes
- Strain relief for the cables provided by cable binder or a clamp
- For MSTB, IC, and GMSTB plugs with and without flange, and pitch of 5.0 and 5.08 mm
- Suitable for cables with a diameter of 4 to 13.5 mm
- Full latching of both half shells of the cable housing



### Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 017918 042035
GTIN	4017918042035
Weight per Piece (excluding packing)	23.650 g
Custom tariff number	85472000
Country of origin	Poland

### Technical data

#### Environmental Product Compliance

China RoHS	No hazardous substances above threshold values
------------	--

#### Dimensions

Pitch	0.00 mm
Dimension a	80 mm

#### General

Range of articles	KGS-MSTB 2,5
-------------------	--------------

# Cable housing - KGS-MSTB 2,5/16 - 1783850

## Technical data

### General


Number of positions	16
Insulating material group	I
Insulating material	ABS
Flammability rating according to UL 94	HB

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Cable housing - KGS-MSTB 2,5/16 - 1783850

### Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC EAC-Zulassung
-------------------

### Accessories

Accessories

Terminal marking


Marker for terminal blocks - SBS 2,5/7,5 - 1007604



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: Plotter, Perforated, Mounting type: Snap into tall marker groove, Snap into flat marker groove, Lettering field: 15 x 7.5 mm

---

Cable housing - KGS-MSTB 2,5/ DST - 1784914



Transparent label carrier, can be marked with marker strips SBS 2.5/7.5

---

Accessories - KD-KGS-MSTB - 1804658



Molded cable strain relief, suitable for KGS-... cable housings, prevents the cable from being bent

---

---