



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	Colour	TAPE DETAILS		PRODUCT USES		MINIMUM SHELF LIFE
				Carrier	Adhesive	Intended Purpose	Key Benefits	
DUCK TAPES								
1500 0401	Waterproof Duck Tape	50mm x 10m	Silver	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0402	Waterproof Duck Tape	50mm x 50m	Silver	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0403	Waterproof Duck Tape	50mm x 25m	Silver	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0412	Waterproof Duck Tape Black	50mm x 5m	Black	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0413	Waterproof Duck Tape Blue	50mm x 5m	Blue	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0414	Waterproof Duck Tape Red	50mm x 5m	Red	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
1500 0415	Waterproof Duck Tape Green	50mm x 5m	Green	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
			Colour	Carrier	Adhesive	Intended Purpose	Key Benefits	
1500 0416	Waterproof Duck Tape White	50mm x 5m	White	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
			Colour	Carrier	Adhesive	Intended Purpose	Key Benefits	
DUCK TAPES								
1500 0421	Waterproof Duck Tape (Flat Pack)	50mm x 3m	Silver	Polyethylene coated polyester fibre	Synthetic rubber	Extra strong all purpose cloth tape for fixing, binding, mounting, repairing, reinforcing, protecting, identifying etc.	Extra strong all purpose Heavy duty, strong and waterproof Durable and weatherproof	18 MONTHS
POWER DUCK TAPES								
1500 0458	Power Duck Tape	50mm x 25m	Silver	Polyethylene coated polyester fibre	Synthetic rubber	Multi-purpose, heavy duty, weatherproof fabric reinforced cloth tape with super strong adhesive that sticks firmly to most surfaces. Repairs, strengthens, binds, protects, seals, packages.	New tape technology, multi-purpose. Easy tear. 100% weatherproof, super strong adhesive. Up to 50% stronger adhesion than standard cloth tapes. 100s of uses around the home, garden, garage and work place.	18 MONTHS
15000459	Power Duck Tape	50mm x 25m	Black	Polyethylene coated polyester fibre	Synthetic rubber	Multi-purpose, heavy duty, weatherproof fabric reinforced cloth tape with super strong adhesive that sticks firmly to most surfaces. Repairs, strengthens, binds, protects, seals, packages.	New tape technology, multi-purpose. Easy tear. 100% weatherproof, super strong adhesive. Up to 50% stronger adhesion than standard cloth tapes. 100s of uses around the home, garden, garage and work place.	18 MONTHS
1500 0462	Virtually Clear Power Duck Tape	50mm x 20m	Clear	Highly transparent polypropylene coated polyester fibre	Clear synthetic rubber	Multi-purpose, heavy duty, weatherproof fabric reinforced cloth tape with super strong UV light resistant adhesive that sticks firmly to most surfaces. Repairs, strengthens, binds, protects, seals, packages.	Advanced technology, multi-purpose. Virtually clear when applied for invisible repairs. Easy tear. 100% weatherproof, super strong UV light resistant adhesive. 100s of uses around the home, garden, garage and work place.	18 MONTHS



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	Colour	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
				Carrier	Adhesive	Intended Purpose	Key Benefits		
MASKING TAPES									
1500 0601	Professional Masking Tape	19mm x 25m	Buff	Crepe paper	Natural rubber	High quality multi purpose masking tape	Clean peel up to 3 days Super sharp edges No residue guaranteed up to 3 days	18 MONTHS	
1500 0611	Professional Masking Tape	25mm x 25m	Buff	Crepe paper	Natural rubber	High quality multi purpose masking tape	Clean peel up to 3 days Super sharp edges No residue guaranteed up to 3 days	18 MONTHS	
1500 0621	Professional Masking Tape	38mm x 25m	Buff	Crepe paper	Natural rubber	High quality multi purpose masking tape	Clean peel up to 3 days Super sharp edges No residue guaranteed up to 3 days	18 MONTHS	
1500 0631	Professional Masking Tape	50mm x 25m	Buff	Crepe paper	Natural rubber	High quality multi purpose masking tape	Clean peel up to 3 days Super sharp edges No residue guaranteed up to 3 days	18 MONTHS	
1500 0652	Masking Tape	25mm x 50m	Buff	Crepe paper	Natural rubber	General purpose masking tape	Remove within 30 hours	18 MONTHS	
1500 0653	Masking Tape	50mm x 50m	Buff	Crepe paper	Natural rubber	General purpose masking tape	Remove within 30 hours	18 MONTHS	
1500 0645	Economy Masking Tape	25mm x 25m	Buff	Crepe paper	Synthetic rubber	Economy masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	
1500 0647	Economy Masking Tape	25mm x 50m	Buff	Crepe paper	Synthetic rubber	Economy masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	
1500 0662	Masking Tape 3 Roll Value Pack	25mm x 25m	Buff	Crepe paper	Synthetic rubber	Low cost entry level masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	
1500 0663	Masking Tape 3 Roll Value Pack	19mm x 25m	Buff	Crepe paper	Synthetic rubber	Low cost entry level masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	
1500 0668	Economy Masking Tape 5 Roll Pack	25mm x 25m	Buff	Crepe paper	Synthetic rubber	Economy masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	
1500 0669	Economy Masking Tape 4 Roll Pack	50mm x 25m	Buff	Crepe paper	Synthetic rubber	Economy masking tape	For best results remove within 3 hours Always remove within 24 hours	18 MONTHS	



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	Colour	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
				Carrier	Adhesive	Intended Purpose	Key Benefits		
SPECIALITY MASKING TAPES									
1500 0831	Drop Cloth	0.55m x 33m	Blue tape/ semi transparent film	Tape - blue crepe paper Film - HDPE	Tape - acrylic	Pre-taped drop cloth for masking larger areas	Saves time, spills and splashes Protects large areas quickly Film clings to surfaces for extra protection	2 YEARS	
1500 0832	Drop Cloth	2.75m x 20m	Blue tape/ semi transparent film	Tape - blue crepe paper Film - HDPE	Tape - acrylic	Pre-taped drop cloth for masking larger areas	Saves time, spills and splashes Protects large areas quickly Film clings to surfaces for extra protection	2 YEARS	
1500 1101	14 Day Masking tape	25mm x 25m	Blue	Crepe paper	Acrylic	Special sunlight resistant masking tape	Super sharp edges No residue guaranteed for up to 14 days Resists sunlight	2 YEARS	
1500 1111	High Tack Exterior Masking Tape	25mm x 25m	Buff	Extra smooth crepe paper with exterior durability	Synthetic rubber	Showerproof masking tape for sticking to most exterior surfaces	Clean peel up to 7 days Durable and strong Ideal for use outside on glass, wood, metal etc.	18 MONTHS	
1500 1121	Curved Edge Masking Tape	25mm x 25m	Yellow	High crepe paper	Natural rubber	Very flexible, highly creped masking tape for curves, corner and archways	Stretches around tricky areas Clean, sharp paint lines Remove just before paint is dry. and within 3 hours of application	18 MONTHS	
1500 1131	Low Tack Stencil Masking Tape	25mm x 25m	White	Flat back paper	Natural rubber	Special low tack masking tape, for use with stencils or on delicate surfaces	Ideal for delicate surfaces Repositionable Easy peel No surface damages	18 MONTHS	
1500 1141	Extra Wide Ultra Low Tack Masking Tape	100mm x 10m	White	Flat back paper	Natural rubber	Low tack extra wide masking tape for masking of large areas (e.g. skirting boards, architrave's)	Clean peel up to 14 days Repositionable Easy and clean removal	18 MONTHS	



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	Colour	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
				Carrier	Adhesive	Intended Purpose	Key Benefits		
CARPET TAPES									
1500 0101	Anti Slip Rug Gripper	254mm x 508mm	White	Cellulose/ polyester mesh	Acrylic	Holding rugs & mats in place	Removable and re-useable For all floor surfaces	2 YEARS	
1500 0111	Rough Surface Carpet Tape	50mm x 10m	Clear with buff liners	PETP/ fabric	Synthetic rubber	Double sided tape for permanent fixing of carpets, flooring tiles and rugs to rough floors	Extra grip for uneven areas For use on cement, metal, tile, stone plywood and painted floors Suitable for high traffic areas	18 MONTHS	
1500 0121	Super Strong Carpet Joining Tape	60mm x 5m	White with white liner	Glass fibre reinforced siliconised paper	Synthetic rubber	Joining seams between carpets	Non stretch Unique fibreglass weave No hot iron needed	18 MONTHS	
1500 0131	Smooth Surface Carpet Tape	50mm x 10m	Clear with buff liner	PETP	Synthetic rubber	Double sided tape for permanent fixing of carpets, flooring tiles and rugs to smooth floors	Strong adhesion for permanent fixing Suitable for carpets, cork tiles and rugs	18 MONTHS	
1500 0161	General Purpose Double Sided Tape	38mm x 5m	Clear with buff liner	Polypropylene	Synthetic rubber	General purpose double sided tape	Strong adhesion Clear tape Multi-use around the home and office	18 MONTHS	
PACKAGING TAPES									
1500 0201	Super Strength Packaging Tape (Dispenser)	50mm x 25m	Tan	Polypropylene	Acrylic	Unique dispenser	Unique dispenser Strong adhesion Resists tears and splits	2 YEARS	
1500 0211	Super Strength Packaging Tape Clear	50mm x 50m	Clear	Polypropylene	Synthetic rubber	General purpose clear packaging tape	Strong adhesion Resists tears and splits Clear	18 MONTHS	
1500 0221	Super Strength Packaging Tape Tan	50mm x 50m	Tan	Polypropylene	Synthetic rubber	General purpose tan packaging tape	Strong adhesion Resists tears and splits Tan	18 MONTHS	
1500 0231	Super Strength Packaging Tape Tan	50mm x 100m	Tan	Polypropylene	Synthetic rubber	General purpose tan packaging tape	Strong adhesion Resists tears and splits Tan	18 MONTHS	
1500 0241	Strong Clear Tape	19mm x 66m	Clear	Polypropylene	Synthetic rubber	General purpose household clear tape	Wide uses around home & office	18 MONTHS	
POLY TAPES (ALL WEATHER)									
1500 0301	All Weather Repair Tape	50mm x 10m	Transparent	Polyethylene	Acrylic	Transparent tape for repairing glass panes of glass, repairing plastic sheets, pool liners, car covers etc.	Thick, strong and waterproof Tough polyethylene tape resistant to water and sunlight	2 YEARS	
1500 0311	All Weather Repair Tape	50mm x 25m	Transparent	Polyethylene	Acrylic	Transparent tape for repairing glass panes of glass, repairing plastic sheets, pool liners, car covers etc.	Thick, strong and waterproof Tough polyethylene tape resistant to water and sunlight	2 YEARS	



HENKEL DUCK TAPE PRODUCT RANGE

DIY TAPE RANGE SUMMARY

HENKEL CODE	PRODUCT DESCRIPTION	DIMENSIONS Width x Length	Colour	TAPE DETAILS			PRODUCT USES		MINIMUM SHELF LIFE
				Carrier	Adhesive	Intended Purpose	Key Benefits		
ELECTRICAL TAPES									
1500 0501	Insulating Electrical Tapes-6xCols	19mm x 3.5m	Various	PVC	Natural rubber	Electrical insulation and other uses around home and car	Insulates up to 600v and 80°C Resists oil, solvents and abrasion	18 MONTHS	
1500 0511	Insulating Electrical Tape	19mm x 10m	Black	PVC	Natural rubber	Electrical insulation and other uses around home and car	Insulates up to 600v and 80°C Resists oil, solvents and abrasion	18 MONTHS	
1500 0521	Insulating Electrical Tape	19mm x 10m	Red	PVC	Natural rubber	Electrical insulation and other uses around home and car	Insulates up to 600v and 80°C Resists oil, solvents and abrasion	18 MONTHS	
1500 0531	Insulating Electrical Tape	19mm x 10m	White	PVC	Natural rubber	Electrical insulation and other uses around home and car	Insulates up to 600v and 80°C Resists oil, solvents and abrasion	18 MONTHS	
MOUNTING TAPES									
1500 0701	Hook & Loop Tape	19mm x 3m	White	Woven nylon fabric	Natural rubber	Self adhesive hook and loop fastening strips	Quick easy storage aid	18 MONTHS	
1500 0731	Flexible Metal Repair Tape	19mm x 1.5m	White	Polyethylene film foam	Natural rubber	Permanent fixing of hooks, signs, numbers	Quick easy alternative to nails and glue (foam pads on a roll)	18 MONTHS	
REPAIR TAPES									
1500 1001	Flexible Metal Repair Tape	50mm x 10m	Metallic	Aluminium foil	Acrylic	Aluminium tape for repairing metal surfaces, e.g. gutters, down pipes, car bodies	For permanent use on metal items Protects, seals and repairs Can be painted	2 YEARS	
1500 1011	Super Strength Wall Repair Tape	50mm x 10m	White	Glass fibre fabric	Acrylic	Joining dry wall seams, covering cracks and patching holes prior to plastering	For permanent patches and repairs Fibre glass reinforced Self adhesive Perfect surface for final finish	2 YEARS	
MISCELLANEOUS TAPES									
1500 0811	Self Adhesive Crack Cover Tape	50mm x 10m	White	Synthetic polypropylene based non woven fabric	Synthetic rubber	Hiding cracks under wallcoverings	Quick and easy No wetting required Prevents wallpaper repairs	18 MONTHS	
1500 0841	Reinforced Strapping Tape	50mm x 25m	Clear/ white	Fibreglass laminated polypropylene	Synthetic rubber	Binding, bundling heavy, valuable or vulnerable items	Added fibreglass for extra strength Resists abrasion damage	18 MONTHS	