

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0444412004](#)
Status: **Active**
Overview: Sabre™ Power Connector
Description: 7.50mm Pitch Sabre™ Receptacle Crimp Housing, UL 94V-0, 4 Circuits

Documents:

3D Model	Packaging Specification PK-44441-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-44441-9999 (PDF)	Product Literature (PDF)
Packaging Specification PK-42295-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	44441
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Positive mating lock and integrated Terminal Position Assurance (TPA) standard.
MolexKits	Yes
Overview	Sabre™ Power Connector
Product Literature Order No	987650-5662
Product Name	Sabre™
UPC	800754366816

Physical

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.399/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +75°C

Electrical

Current - Maximum per Contact	18.0A
-------------------------------	-------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-42295-001, PK-44441-001
Product Specification	PS-44441-9999
Sales Drawing	SD-44441-2004



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[44441](#) Series

Mates With

Plug Housing [43680-2004](#). 4 Circuit, UL 94V-0 Vertical or Right Angle Headers [43160](#). 4 Circuit, UL 94V-0 Right Angle, UL1977 finger proof compliant [46007](#)

Use With

Female Crimp Terminals [43375](#)

This document was generated on 09/21/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION