

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020119](#)  
**Status:** **Active**  
**Overview:** [C-Grid® Products](#)  
**Description:** SL™ Crimp Terminal, Series 71851, Female, with 0.38µm Selective Gold (Au) Plated Contact, 24-30 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-71851 \(PDF\)](#)  
[Product Specification PS-70400 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [71851](#)  
 Application Signal  
 Crimp Quality Equipment Yes  
 Overview [C-Grid® Products](#)  
 Packaging Alternative [16-02-1109 \(Loose\)](#)  
 Product Name SL™  
 UPC 800753595729

**Physical**

Gender Female  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Net Weight 0.060/g  
 Packaging Type Reel  
 Plating min - Mating 0.381µm  
 Plating min - Termination 1.905µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 1.52mm max.  
 Wire Size AWG 24, 26, 28, 30  
 Wire Size mm² N/A

**Solder Process Data**


Lead-free Process Capability N/A

**Material Info**

Engineering Number 71851-0006

**Reference - Drawing Numbers**

Product Specification PS-70400, PS-71851  
 Sales Drawing SD-71851-0006



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
 ELV

Green Image  
 Not Relevant

**Search Parts in this Series**

[71851 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Insertion Tool	<a href="#">0011020022</a>
Extraction Tool	<a href="#">0011030036</a>
Hand Crimp Tool For SL™ Crimp Terminals	<a href="#">0638258800</a>
FineAdjust™ Applicator, 24-30 AWG Wire	<a href="#">0639001500</a>
FineAdjust™ Applicator for Female	<a href="#">0639003100</a>

Crimp Terminal,  
24-30 AWG Wire  
T2 Terminator 0639103100  
Tooling Die

This document was generated on 09/22/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**