

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002065102**
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>1561</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Standard .062" Pin and Socket Power Connectors</u>
Packaging Alternative	<u>02-06-5101 (Reel)</u>
Product Name	Standard .062"
UPC	800754227582

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.080/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Material Info

Engineering Number 1561-(P561)L

Reference - Drawing Numbers

Packaging Specification PK-1190-003
 Sales Drawing SD-1561-*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

1561 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Insertion Tool	<u>0011020001</u>
Hand Crimper - DISTRIBUTION ONLY	<u>0638111000</u>
Manual Extraction Tool	<u>0011030002</u>
Hand Crimp Tool for Standard 1.57mm Pin and Socket	<u>0638191300</u>

This document was generated on 10/24/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION