

**Product Description:**

Performance - that's what the Uni-Fit™ range of commercial downlights stands for. Featuring ThermoTec™ technology, integrated driver and high quality LED chips to deliver serious lumen performance. The Uni-Fit range is the ideal cost effective solution for new or existing installations where traditional compact fluorescent downlights need upgrading to more efficient LED technology.

**Product Image:****Product Features:**

- Multiple sizes and wattages available to suit all new and retrofit installation lighting requirements
- ThermoTec™ technology utilises a combination of highly efficient LED light source, aluminium heat sinking and thermoplastic material for longer life and consistent performance
- Compact integrated driver allows for easy installation
- Life not affected by frequent switching e.g. when used with occupancy controls
- Pre-wired with 500mm 2 core cable
- 1.5kV surge protection
- 3 year warranty

25W Integrated IP44 Dimmable LED Downlight

**Product Specs:**

<b>Technology</b>	LED	<b>Number of LEDs</b>	70
<b>Luminaire Distribution</b>	Direct	<b>Lifetime L70 (hrs)</b>	25000
<b>Input Voltage</b>	220~240V AC	<b>Input Frequency</b>	50/60HZ
<b>Surge Protection (kV)</b>	1.5	<b>Power Factor</b>	0.9
<b>Dimmable</b>	Yes	<b>IP Rating</b>	IP40
<b>Optic Material</b>	PC	<b>Cutout Diameter (mm)</b>	200
<b>Overall Diameter (mm)</b>	230	<b>Overall Height (mm)</b>	60
<b>Recess Depth (mm)</b>	70		

**SKU Table and Ordering**

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-DDL25/40	25W	1800lm	72	4000K	80	100°	6

**Compliance & Approvals:**

## Warranty

---

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

### UK Enlite Sales

16 Alban Park Hatfield Road St. Albans  
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

### UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn  
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21