

### Product Description:

The Enlite range of Slim-Fit™ low profile downlights are engineered to deliver superior light output and uniformity utilising the latest edge-lit LED technology. At only 25mm deep including bracket, they are an ideal solution where ceiling voids are limited but high lumen output is required.

### Product Image:




### Product Features:

- Low cost energy saving alternative to compact fluorescent fittings
- Edge-lit low profile ideal for installations with limited recess space (25mm) and shallow ceiling voids
- Plug and play remote driver for easy installation (40mm space required)
- Separate triac dimmable driver available
- Life not affected by frequent switching e.g. when used with occupancy controls
- 1.5kV surge protected
- IP44 rated
- 3 year warranty

6W IP44 Round Low Profile LED Downlight

### Line Drawing Image



### Product Specs:

Technology	LED	Number of LEDs	30
Lifetime L70 (hrs)	25000	Input Voltage	100~240V AC
Input Frequency	50/60HZ	Surge Protection (kV)	1.5
Power Factor	0.8	Dimmable	No
IP Rating	IP44	Operating Temp. (Max) °C	40
Cutout Diameter (mm)	107	Overall Diameter (mm)	120
Overall Height (mm)	25	Recess Depth (mm)	40

### SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-PL06B/30	6W	300lm	50	3000K	80	110°	6
EN-PL06B/40	6W	330lm	55	4000K	80	110°	6
EN-PL06B/65	6W	350lm	58.33	6500K	80	110°	6

### Compliance & Approvals:



## Warranty

---

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

### UK Enlite Sales

16 Alban Park Hatfield Road St. Albans  
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

### UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn  
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21