

### Product Description:

The new IP65 driverless range of QuaZar™ floodlights incorporate the latest in high voltage LED technology. With their ultra slim profile and high performance, now you can light your external areas and gardens without sacrificing the appearance. Available in 10W, 20W, 30W and 50W versions including black and white housing finishes to suit external fascias.

### Product Image:



50W Adjustable IP65 Driverless LED Floodlight

### Product Features:

- IP65 rated LED floodlight with ultra slim design for minimal visual impact
- High voltage LED chips - no driver for improved reliability
- IK08 rated aluminium housing and tempered glass provides excellent protection
- Available in black and white finish housing
- Pre-wired with 600mm of cable
- 1.5kV surge protection
- 2 year warranty

### Product Specs:

<b>Technology</b>	LED	<b>Number of LEDs</b>	1
<b>Lifetime L70 (hrs)</b>	25000	<b>Input Voltage</b>	180~240V AC
<b>Input Frequency</b>	50/60HZ	<b>Surge Protection (kV)</b>	1.5
<b>Power Factor</b>	0.8	<b>Dimmable</b>	No
<b>IP Rating</b>	IP65	<b>Optic Material</b>	Glass
<b>Width (mm)</b>	274	<b>Height (mm)</b>	190

### SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-FLHV50W/40	50W	4500lm	90	4000K	70	120°	6
EN-FLHV50BLK/40	50W	4500lm	90	4000K	70	120°	6
EN-FLHV50W/30	50W	4500lm	90	3000K	70	120°	6
EN-FLHV50BLK/30	50W	4500lm	90	3000K	70	120°	6
EN-FLHV50W/65	50W	4500lm	90	6500K	70	120°	6
EN-FLHV50BLK/65	50W	4500lm	90	6500K	70	120°	6

### Compliance & Approvals:



## Warranty

---

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

### UK Enlite Sales

16 Alban Park Hatfield Road St. Albans  
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

### UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn  
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21