

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0002096106](#)  
**Status:** **Active**  
**Overview:** Standard .093" Pin and Socket Connectors  
**Description:** 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Gold (Au) Plated Brass Contact, 14-20 AWG, Bag

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-1190-003 \(PDF\)](#)  
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-1190-001 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">1190</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .093" Pin and Socket Connectors</a>
Packaging Alternative	<a href="#">02-09-6100 (Reel)</a>
Product Name	Standard .093"
UPC	800753615465

**Physical**


Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.414/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.254µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

**Material Info**

Engineering Number 1190-(550)L

**Reference - Drawing Numbers**

Packaging Specification	PK-1190-001, PK-1190-003
Product Specification	PS-02-09
Sales Drawing	SD-1190-*



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[1190 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Insertion Tool	<a href="#">0011020003</a>
Hand Crimper - DISTRIBUTION ONLY	<a href="#">0638111000</a>
Extraction Tool	<a href="#">0011030006</a>
Hand Crimp Tool	<a href="#">0638191100</a>
Extractor Tool for .093 and	<a href="#">0638240200</a>

This document was generated on 10/25/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**