

Acer S220HQLBrbd(ET.WSOHE.B01)

S220HQLBbd - LED monitor - 21.5" - 1920 x 1080 FullHD - 200 cd/m² - 100000000:1 (dynamic) - 5 ms - DVI -D,VGA - black



Acer S series monitor is very slim yet spacious display that is great for multitasking and web browsing. High-definition visual leaps to life and an extremely high contrast ratio. You'll appreciate both the imagery and the look of this streamlined yet powerful Acer monitor!

Key Selling Points

- Ultra-thin,space-saving design
- Earth-friendly technologies
- Impressive performance

Product Features

Ultra-thin,space-saving design

The S series is designed to fit nicely in your living space,be it at home or in a SOHO,public area,or front-desk setting. Ultra-thin and ultra-elegant,the display is built around a sense of simple modernism.

Earth-friendly technologies

The S series uses mercury-free materials and white LED technology for up to 68% lower power consumption,giving you big savings while helping preserve nature's energy resources. By meeting ENERGY STAR requirements,the S series considers the environment.

Impressive performance

Games are more exciting and entertainment is truly cinematic. In addition,an DVI interface connects you to the high-definition devices,while an astounding contrast ratio delivers fantastic clarity.

Main Specifications

Product Description	Acer S220HQLBrbd - LED monitor - 21.5"
Device Type	LED-backlit LCD monitor - 21.5"
Aspect Ratio	Widescreen - 16:9
Native Resolution	Full HD 1920 x 1080 at 60 Hz
Brightness	200 cd/m ²
Contrast Ratio	100000000:1 (dynamic)
Response Time	5 ms
Colour Support	16.7 million colours
Input Connectors	DVI -D,VGA
Display Position Adjustments	Tilt
Colour	Black
Environmental Standards	ENERGY STAR Qualified
Compliant Standards	MPR II
Manufacturer Warranty	3 years warranty

Extended Specification

General

Display Type	LED-backlit LCD monitor / TFT active matrix
Diagonal Size	21.5"

Aspect Ratio	Widescreen - 16:9
Native Resolution	Full HD 1920 x 1080 at 60 Hz
Brightness	200 cd/m ²
Contrast Ratio	100000000:1 (dynamic)
Colour Support	16.7 million colours
Response Time	5 ms
Backlight Technology	LED backlight
Features	HDCP,Acer EcoDisplay,Acer Adaptive Contrast Management (ACM)
Colour	Black

Connectivity

Interfaces	VGA DVI-D
------------	--------------

Mechanical

Display Position Adjustments	Tilt
Tilt Angle	20

Miscellaneous

Cables Included	1 x VGA cable
Compliant Standards	MPR II

Power

Power Supply	External
Voltage Required	AC 120/230 V
Power Consumption Operational	22 Watt
Power Consumption Stand by / Sleep	0.6 Watt

Environmental Standards

ENERGY STAR Qualified	Yes
-----------------------	-----

Manufacturer Warranty

Service &Support	Limited warranty - 3 years - carry-in
------------------	---------------------------------------

What's in the box

Acer S220HQLBrbd
VGA cable
External power adapter

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet