

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0503948052](#)
Status: **Active**
Overview: [Milli-Grid™ Connector System](#)
Description: [Milli-Grid™ Crimp Terminal, Female, 0.76µm Select Gold, Reel, Lead free](#)

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Specification PS-51110-001-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	50394
Application	Signal
Crimp Quality Equipment	Yes
Overview	Milli-Grid™ Connector System
Packaging Alternative	50394-8200 (Loose)
Product Literature Order No	987650-1991
Product Name	Milli-Grid™
UPC	800753576209

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.023/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	0.5A, 1.5A, 1.0A, 2.0A
Voltage - Maximum	125V


Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-51110-001-001
Sales Drawing	SD-50394-8XXX-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[50394 Series](#)

Use With

Milli-Grid™ Receptacle Housing [51110](#) ,
[151100](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Crimp Terminals	0638190100
Manual Extraction Tool	0638131400

FineAdjust™	<u>0639005200</u>
Applicator for 2.00mm Pitch Wire- to-Board Crimp Terminals, 24-30 AWG Wire	
T2 Terminator Die	<u>0639105200</u>

This document was generated on 11/17/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION