

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550124](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® High Pressure Crimp Terminal 7879, 22-30 AWG, Reel Selective Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879-001 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
 Series [7879](#)
 Application [Signal](#)
 Crimp Quality Equipment [Yes](#)
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-55-0129 \(Loose\)](#)
 Product Name [KK® High Pressure](#)
 UPC [800753614185](#)

Physical

Gender [Female](#)
 Material - Metal [Brass](#)
 Material - Plating Mating [Gold](#)
 Material - Plating Termination [Tin](#)
 Net Weight [0.117/g](#)
 Packaging Type [Reel](#)
 Plating min - Mating [0.381µm](#)
 Plating min - Termination [2.540µm](#)
 Termination Interface: Style [Crimp or Compression](#)
 Wire Insulation Diameter [1.57mm max.](#)
 Wire Size AWG [22, 24, 26, 28, 30](#)
 Wire Size mm² [N/A](#)

Solder Process Data


Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [7879-1\(P208\)](#)

Reference - Drawing Numbers

Product Specification [PS-7879-001](#)
 Sales Drawing [SD-7879](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7879 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Terminator Die	0011402251
Extraction Tool	0011030022
Insertion Tool	0638120000
Hand Crimp Tool	0638190800
Mini-Mac™	0638915100
Applicator	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION