

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020088](#)  
**Status:** **Active**  
**Overview:** C-Grid® Products  
**Description:** SL™ Crimp Terminal 70058, 22-24 AWG, Reel Selective Gold (Au)

**Documents:**

[Drawing \(PDF\)](#) [Test Summary TS-70058-001-001 \(PDF\)](#)  
[Product Specification PS-70058-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-70400-001 \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [70058](#)  
 Application Signal  
 Comments Use with CyClone Panel-to-Panel Connector [73099](#)  
 Crimp Quality Equipment Yes  
 Overview [C-Grid® Products](#)  
 Packaging Alternative [16-02-0104 \(Loose\)](#)  
 Product Name SL™  
 UPC 800753596030

**Physical**

Gender Female  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Net Weight 0.073/g  
 Packaging Type Reel  
 Plating min - Mating 0.762µm  
 Plating min - Termination 1.905µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 1.63mm max.  
 Wire Size AWG 22, 24  
 Wire Size mm² N/A

**Material Info**

Engineering Number 70058-0026

**Reference - Drawing Numbers**

Product Specification PS-70058-001, PS-70400-001  
 Sales Drawing SD-70058-0026  
 Test Summary TS-70058-001-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[70058 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
Insertion Tool	<a href="#">0011020022</a>
Hand Crimp Tool	<a href="#">0638118700</a>
FineAdjust™	<a href="#">0639023200</a>
Applicator for Crimp Terminals 20-24 AWG Wire	
T2 Terminator for Female Crimp Terminal	<a href="#">0639123200</a>

This document was generated on 11/18/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**