

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190690212](#)  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** Krimptite™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.94mm, Mylar Tape Carrier

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19069](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Solderless Terminals](#)  
 Product Name Krimptite™  
 Type Ring  
 UPC 800753068162

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.453/g  
 Packaging Type Adhesive Tape on Reel  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 10 (M5)  
 Termination Interface: Style Crimp or Compression  
 Wire Size AWG 10, 12  
 Wire Size mm<sup>2</sup> 4.00-6.00

**Solder Process Data**


Lead-freeProcess Capability N/A

**Material Info**

Engineering Number C-128-10T

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001  
 Sales Drawing SD-19069-020



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[19069 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<a href="#">0190270088</a>
Mini-Mac™ Applicator	<a href="#">0638851000</a>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**