



MASTER LEDluster DiamondSpark

MAS LEDlustre DT 6-40W B22 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDluster bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDlusters drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear glass bulb fits all existing fixtures with an E14, E27 and B22 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost.

Product data


General Information		Color rendering index (nom.)	
Cap base	B22 [B22]	80	
Bulb shape	P48	LLMF at end of nominal lifetime (nom.)	
Nominal lifetime (nom.)	25000 h	70 %	
Switching cycle	50000X	Operating and Electrical	
Technical type	6-40W	Input frequency	50-60 Hz
Light Technical		Power (Rated) (Nom)	6 W
Luminous flux (nom.)	470 lm	Lamp current (nom.)	35 mA
Luminous flux (rated) (nom.)	470 lm	Wattage equivalent	40 W
Colour designation	Warm white (WW)	Starting time (nom.)	0.5 s
Correlated colour temperature (nom.)	2200-2700 K	Warm-up time to 60% light (nom.)	instant full light
Luminous efficacy (rated) (nom.)	75 lm/W	Power factor (nom.)	0.7
Colour consistency	<6	Voltage (Nom)	220-240 V

MASTER LEDluster DiamondSpark

Temperature	
T-Case maximum (nom.)	95 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Suitable for accent lighting	No
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	6 kWh

Product Data	
Full product code	871869647477800
Order product name	MAS LEDlustre DT 6-40W B22 P48 CL
EAN/UPC – product	8718696474778
Order code	47477800
Local Code	MLED6WLUSDT22
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001157302
Net weight (piece)	0.072 kg

Dimensional drawing



LED DT 6-40W B22 P48 CL

Product	D	C
MASTER LEDlustre DT 6-40W B22 P48 CL	48 mm	92 mm

