

## Basic

Brand Name:	HP
Environmentally Friendly:	Yes
Form Factor:	Small Form Factor
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 510
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
HDMI:	Yes
Number of USB 2.0 Ports:	6
Number of USB 3.0 Ports:	2
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	G4400
Processor Speed:	3.30 GHz
Processor Type:	Pentium
Product Family:	Business Desktop 280 G2
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	8
VGA:	Yes

## Display & Graphics

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 510
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

## General Information

Brand Name:	HP
Manufacturer Part Number:	Y5P88EA#ABU
Manufacturer Website Address:	<a href="http://www.hp.com">http://www.hp.com</a>
Manufacturer:	HP Inc.
Product Line:	Business Desktop
Product Name:	Business Desktop 280 G2 Desktop Computer
Product Series:	280 G2
Product Type:	Desktop Computer

## Interfaces/Ports

HDMI:	Yes
Number of USB 2.0 Ports:	6
Number of USB 3.0 Ports:	2
Total Number of USB Ports:	8
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"><li>• Business Desktop 280 G2 Desktop Computer</li><li>• Keyboard</li></ul>

## Physical Characteristics

Depth:	290 mm
Form Factor:	Small Form Factor
Height:	100 mm
Weight (Approximate):	3.66 kg
Width:	270 mm

## Processor & Chipset

Processor Manufacturer:	Intel
Processor Model:	G4400

Processor Speed: 3.30 GHz  
Processor Type: Pentium

**Software**

Operating System Architecture: 64-bit  
Operating System Platform: Windows  
Operating System: Windows 10 Pro

**Storage**

Optical Drive Type: DVD-Writer  
Optical Media Supported: DVD-RAM/±R/±RW  
Total Hard Drive Capacity: 500 GB

**Warranty**

Limited Warranty: 1 Year