

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192110001](#)  
**Status:** **Active**  
**Overview:** [Wire Pins](#)  
**Description:** Krimptite™ Wire Pin Terminal for 12-10 AWG Wire

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Crimp Terminals
Series	<a href="#">19211</a>
Application	Power
Comments	Pin Length 11.43mm
Crimp Quality Equipment	Yes
Overview	<a href="#">Wire Pins</a>
Packaging Alternative	<a href="#">19211-0002</a> (Adhesive Tape on Reel)
Product Name	Wire Pin
UPC	800755061994

**Physical**

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	1.465/g
Packaging Type	Bag
Plating min - Mating	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size AWG	10, 12

**Material Info**

Engineering Number	WP-1210
--------------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19211-002



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

**Search Parts in this Series**

[19211](#) Series

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.*

**Global**

Description	Product #
PremiumGrade™ Hand Crimp Tool	<a href="#">0640030100</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640070100</a>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**