

## Basic

Brand Name:	Lenovo
Colour:	Black
DisplayPort:	Yes
Environmentally Friendly:	Yes
Form Factor:	Small Form Factor
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
Product Family:	ThinkCentre M700
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	6
VGA:	Yes
Wireless LAN:	No

## Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

## General Information

Brand Name:	Lenovo
Manufacturer Part Number:	10GT005AUK
Manufacturer Website Address:	<a href="http://www.lenovo.com/uk/en/">http://www.lenovo.com/uk/en/</a>
Manufacturer:	Lenovo Group Limited
Product Line:	ThinkCentre
Product Model:	10GT005AUK
Product Name:	ThinkCentre M700 10GT005AUK Desktop Computer
Product Series:	M700
Product Type:	Desktop Computer

## Interfaces/Ports

DisplayPort:	Yes
Number of USB 2.0 Ports:	2
Number of USB 3.0 Ports:	4
Total Number of USB Ports:	6
VGA:	Yes

## Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Environmental Certification:	GREENGUARD
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"><li>• ThinkCentre M700 10GT005AUK Desktop Computer</li><li>• Keyboard</li><li>• Mouse</li></ul>

## Network & Communication

Wireless LAN:	No
---------------	----

## Physical Characteristics

Colour:	Black
Depth:	356.9 mm

Form Factor:	Small Form Factor
Height:	87.9 mm
Weight (Approximate):	5.58 kg
Width:	338.1 mm

#### **Processor & Chipset**

Processor Generation:	6th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3

#### **Software**

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

#### **Storage**

Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	500 GB

#### **Warranty**

Limited Warranty:	3 Year
-------------------	--------