



Plug and Play **SECURE** and Walk Away

- Step 1 -

Pick your Alarm System

Note: All Control Panels have internal sirens

- Step 2 -

Add 'Live' and/or Replica Sirens

Note: All sirens below (excluding the Replica Siren) can be used as stand-alone alarm systems when connected to Door/Window Sensors and PIRs

- Step 3 -

Extend your home security & alert system with additional accessories

Note: Maximum no. of accessories: **Valiant** – 40 Sensors, 10 Remote Controls
Garrison – 50 Sensors, 10 Remote Controls
Vault & Invincible - 50 Sensors, 10 Remote Controls, 50 Tags



VALIANT - SIREN STARTER KIT
Contents: Solar Charged Siren, Pet Friendly PIR Sensor, Magnetic Door/Window Sensor, Remote Control. Can also be used as an expansion pack for any of the below alarm systems



SOLAR CHARGED OUTDOOR SIREN
110dB Siren with flashing 24/7 comfort lights and battery included



Pet Friendly PIR Sensor



Ceiling PIR Sensor



Curtain PIR Motion Sensor



GARRISON - SMARTPHONE GSM/SMS COMMUNICATING KIT
Set up via App or SMS text. Contents: Touch Control Keypad, Pet Friendly PIR Sensor, Magnetic Door/Window Sensor, 2 x Remote Controls



INTERNAL PLUG-IN SIREN
90dB Siren. Night light function. Portable and ideal for larger properties where an additional siren is needed.



Door/Window Sensor



Vibration Sensor



Water Detector



VAULT - SMARTPHONE GSM/SMS COMMUNICATING KIT WITH LED DISPLAY
Set-up via App or SMS text. Contents: Control Panel, Pet Friendly PIR Sensor, Magnetic Door/Window Sensor, 2 x Remote Controls and 2 x RFID Tags



MAINS POWERED OUTDOOR SIREN
105dB Siren. LED lights flash when the system is in arm mode.



Smoke Detector



IP HD Camera



Range Extender



INVINCIBLE - DUAL NETWORK COMMUNICATING KIT GSM/GPRS, PSTN (LANDLINE) WITH PROGRAMMABLE CONTROL PANEL
Set up via Control Panel. Contents: LCD Control Panel, Pet Friendly PIR Sensor, Magnetic Door/Window Sensor, 2 x Remote Controls and 2 x RFID Tags



OUTDOOR REPLICA SIREN
Flashing comfort light gives the appearance of being a 'Live' Siren. Use as an additional visual deterrent on the rear of a property or outbuilding.



RFID Contactless Tag



Remote Control



RFID Keypad



Personal Alert Button

ALARM TECHNICAL MATRIX

	Valiant	Garrison	Vault	Invincible
Kit Contents				
Solar Siren	1			
Touch Control Panel		1	1	1
Pet Friendly PIR Sensor	1	1	1	1
Door/Window Sensor	1	1	1	1
Remote Control	1	2	2	2
Contactless RFID Tag			2	2
Connectivity				
GSM/SMS		•	•	•
GPRS				•
PSTN (Landline)				•
App Control		•	•	•
Notification Method	> External Siren	> Internal Siren > SMS Alert > Phone Call	> Internal Siren > SMS Alert > Phone Call	> Internal Siren > SMS Alert > GPRS Push Notifications > Phone Call
Remote Monitoring				
Listen-In		•	•	•
Two-Way Talk		•	•	•
CMS Centre Compatible				•
Features				
Internal Siren		•	•	•
External Siren	•			
Siren Volume (dB)	110dB	90dB	95dB	95dB
Adjustable Siren Volume	•	•	•	•
Mute Arm/Disarm	•	•	•	•
Anti Tamper	•	•	•	•
Part Arm		•	•	•
Zone Naming (Max No.)		50	50	50
Voice Memo		•	•	•
Entry/Exit Delay		•	•	•
GSM Recorded Message Notification		•	•	•
SMS Text Alarm Event Log		•	•	•
Voice Memo		•	•	•
Personalised SMS Notifications			•	•
PSTN (Landline) Recorded Message Notifications				•
Programmable Control Panel				•
LCD Display				•
LED Display			•	
Control Panel Event Log (max no.)				150
SOS Panic Facility	> Remote Control	> Remote Control	> Remote Control	> Remote Control > Control Panel
Radio Frequency	433 MHz	433 MHz	433 MHz	433 MHz
Transmitting Distance	≤ 80 metres	≤ 80 metres	≤ 80 metres	≤ 80 metres
Max No. Accessories	> 40 Wireless Sensors > 10 Remote Controls	> 50 Wireless Sensors > 10 Remote Controls	> 50 Wireless Sensors > 50 Contactless RFID Tags > 10 Remote Controls	> 50 Wireless Sensors > 50 Contactless RFID Tags > 10 Remote Controls