

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1502000002](#)
Status: **Active**
Overview: [Ditto™ Wire-to-Wire Interconnects](#)
Description: [Ditto™ Genderless Crimp Terminal, Tin Brass, Preplated Tin, 24-26 AWG](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-150197-0000 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	150200
Application	Power
Comments	See Product Specification for maximum current rating by circuit size and AWG.
Crimp Quality Equipment	Yes
Overview	Ditto™ Wire-to-Wire Interconnects
Product Name	Ditto™
UPC	889056215657

Physical

Durability (mating cycles max)	25
Gender	Genderless
Material - Metal	Tin Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.156/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.05-1.50mm
Wire Size AWG	24, 26
Wire Size mm ²	N/A


Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	350V AC/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-150197-0000
Sales Drawing	SD-150200-0000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[150200](#) Series

Use With

Ditto™ Genderless Crimp Housing [150170](#) , [150201](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Ditto Wing Genderless Interconnects Terminal, 24–26 AWG	0638278600
FineAdjust™ Applicator for	0639038500

Male and Female
Terminal Ditto™
Interconnects, 24-26
AWG

This document was generated on 07/14/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION