

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000220](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: [Mini-Fit® Male Crimp Terminal, Phosphor Bronze, Gold \(Au\), 18-24 AWG, Bag](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-5556-003 \(PDF\)](#)
[Product Specification PS-5556-002 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [5558](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [Mini-Fit Jr.™ Power Connectors](#)
Packaging Alternative [39-00-0219 \(Reel\)](#)
Product Name [Mini-Fit®](#)
UPC [800754396356](#)

Physical

Durability (mating cycles max) [30](#)
Gender [Male](#)
Material - Metal [Phosphor Bronze](#)
Material - Plating Mating [Gold](#)
Material - Plating Termination [Tin](#)
Net Weight [126.914/mg](#)
Packaging Type [Bag](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.30-3.10mm](#)
Wire Size AWG [18, 20, 22, 24](#)
Wire Size mm² [N/A](#)

Electrical


Current - Maximum per Contact [9.0A](#)
Voltage - Maximum [600V](#)

Material Info

Old Part Number [5558PBGSL](#)

Reference - Drawing Numbers

Packaging Specification [PK-5556-003](#)
Product Specification [PS-5556-002](#)
Sales Drawing [SD-5558-002](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female	0638190900

Crimp Terminals,
16-24 AWG Wire
Extraction Tool 0011030044

Japan

Description	Product #
--------------------	------------------

Handtool (Straight Action)	<u>0570225500</u>
-------------------------------	-------------------

Hand Crimp Tool	<u>0570265000</u>
-----------------	-------------------

This document was generated on 08/10/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION