

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0643221019](#)  
**Status:** **Active**  
**Overview:** CMC and CMX Sealed, Hybrid, Modular Connectors  
**Description:** 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.35mm<sup>2</sup>

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">64322</a>
Application	Signal
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C. Current max = 6A for 0.635mm Terminal(0.75mm <sup>2</sup> wire)
Crimp Quality Equipment	Yes
Overview	<a href="#">CMC and CMX Sealed, Hybrid, Modular Connectors</a>
Product Name	CMC, CP Terminal
UPC	883906129460

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.160/g
Packaging Type	Reel
Plating min - Mating	1.524µm, 3.048µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25mm-1.40mm
Wire Size AWG	22, 24
Wire Size mm <sup>2</sup>	0.35

**Electrical**

Current - Maximum per Contact	6.0A
Voltage - Maximum	14V DC


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-64322-001
---------------	--------------



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

**Search Parts in this Series**

[64322](#) Series

**Mates With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

**Use With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FineAdjust™	<u>0639021900</u>
Applicator for CP	
0.6mm Terminal	
Extraction Tool	<u>0638132400</u>
Hand Crimp Tool	<u>0638119100</u>

This document was generated on 07/18/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**