

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0349003120](#)  
**Status:** **Active**  
**Overview:** MXP120™ Sealed Connector System  
**Description:** MXP120™ Sealed Receptacle, 3 Circuit, Black Housing, Key A, Black Insert

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34900-0001-CH (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31301-898 (PDF)</a>
<a href="#">Product Specification PS-34900-0001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34900-0001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**

Product Family	Crimp Housings
Series	34900
Application	Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	<a href="#">MXP120™ Sealed Connector System</a>
Polarization	A
Product Literature Order No	987650-7994
Product Name	MXP120™ Sealed
UPC	889056197694

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.938/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +125°C

**Electrical**

Current - Maximum per Contact	13.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-34900-0001, AS-34900-0001-CH
Packaging Specification	PK-31301-898
Product Specification	PS-34900-0001
Sales Drawing	SD-34900-2001, SD-34900-6001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS  
ELV

Green Image  
Compliant

**Search Parts in this Series**

[34900 Series](#)

**Mates With**

MXP120™ Male Blade Connector  
34899-3020 , 34899-3040

**Use With**

1.2 LL SWS from Tyco and Kostal