


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0932880001](#)  
**Status:** **Active**  
**Overview:** SRC - Sealed Rectangular Connectors  
**Description:** SRC Housing, Male, 84 Pin Signal (84 x MX150™ Terminals), Nylon, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 850830010 (PDF)</a>
<a href="#">Product Specification 850710010 (PDF)</a>	<a href="#">Test Summary STR-1389 (PDF)</a>
<a href="#">Product Specification 850710020 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 850830010 (PDF)</a>	<a href="#">Product Literature (PDF)</a>



**General**

Product Family	Crimp Housings
Series	93288
Application	Signal, Wire-to-Wire
Comments	Polarized to mating part
More Detailed Tech Information	Current (max.) for 84 way fully loaded 6A with 30° temp rise (AWG 14 MX150)
Overview	<a href="#">SRC - Sealed Rectangular Connectors</a>
Product Literature Order No	987650-7391
Product Name	SRC
UPC	884982405233

**Physical**

Circuits (maximum)	84
Circuits Detail	84 x MX150™
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	149.600/g
Number of Rows	14
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

**Electrical**

Current - Maximum per Contact	18.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	850830010
Product Specification	850710010, 850710020, 850830010
Sales Drawing	932880001
Test Summary	STR-1389

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[93288 Series](#)

**Mates With**

[93287 SRC Receptacle Housing](#)

**Use With**

[33000 MX™ Blade Terminal](#)