

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934457111](#)  
**Status:** **Active**  
**Overview:** ML-XT™ Sealed Connection System  
**Description:** ML-XT™ Sealed 18 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option A, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 934430002 (PDF)</a>
<a href="#">Product Specification 934430010 (PDF)</a>	<a href="#">Packaging Specification 934430010 (PDF)</a>
<a href="#">Application Specification 934430010 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Housings
Series	<a href="#">93445</a>
Application	Power, Signal, Wire-to-Wire
Overview	<u>ML-XT™ Sealed Connection System</u>
Product Name	ML-XT™
UPC	889056263511

**Physical**

Circuits (maximum)	18
Color - Resin	Black
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	18.230/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

**Electrical**

Current - Maximum per Contact	13.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	934430010
Packaging Specification	934430002, 934430010
Product Specification	934430010
Sales Drawing	934430070

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[93445](#) Series

**Mates With**

ML-XT™ Sealed 18 Circuit Receptacle Housing [93444-7111](#)

**Use With**

ML-XT™ Female (Socket) Terminal [84525-0009](#) (Nickel), ML-XT™ Female (Socket) Terminal [84525-0032](#) (Selective Gold), ML-XT™ Blind Cavity Plug [93494-1000](#)