


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934441201](#)
Status: **Active**
Overview: ML-XT™ Sealed Connection System
Description: ML-XT™ Sealed 2 Circuit Receptacle Housing, Pre-Assembled with Large Rear Seal and Cover, Black

Documents:

Drawing (PDF)	Packaging Specification 934430010 (PDF)
Product Specification 934430010 (PDF)	Test Summary STR-1707 (PDF)
Application Specification 934430010 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 934430002 (PDF)	



Series image - Reference only

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	63824-5300
Overview	<u>ML-XT™ Sealed Connection System</u>
Product Name	ML-XT™
UPC	887191604237

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.777/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002, 934430010
Product Specification	934430010
Sales Drawing	934430010
Test Summary	STR-1707

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[93444 Series](#)

Mates With

[ML-XT™ Sealed 2 Circuit Plug Housing
93445-1201](#)

Use With

[ML-XT™ Male \(Pin\) Terminal 84524-0004](#)
(Nickel), [ML-XT™ Male \(Pin\) Terminal
84524-0014](#) (Selective Gold), [ML-XT™ 2
Circuit Receptacle Wedgelock 93447](#) , [ML-
XT™ Blind Cavity Plug 93494-1000](#)