

General Information

Extended Product Type:	CS
Product ID:	1SNK900101R0000
EAN:	3472599102194
Catalog Description:	CS Circuit Separator without spacing loss - Dark Grey
Long Description:	- The CS circuit separator avoids the derating of terminal blocks when cut jumper bars JB are used, - Compatible with feed-through terminal blocks up to 16 mm ² 4 AWG, - Without spacing loss.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Circuit Separators

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097
Color:	Dark Grey

Dimensions

Product Net Height:	14.8 mm
Product Net Length:	20.5 mm
Product Net Depth:	20.5 mm
Product Net Weight:	0.2 g
Product Net Width:	0 mm

Technical

Spacing:	0 mm
Function:	Circuit Separators
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ES10-ST JB10 JB16 ZDP2.5-11 ZDP2.5-22 ZP2.5 ZP2.5-3P ZP2.5-4P ZP2.5-PE ZP2.5-PE-3P ZP2.5-PE-4P ZP2.5-SP ZS10 ZS16 ZS16-PE ZS25 ZS25-PE ZS4 ZS4-PE ZS6 ZS6-3S ZS6-3S-PE ZS6-4S ZS6-4S-PE ZS6-PE ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160018D0201
RoHS Information:	1SND230495F0202

Classifications

E-nummer:	2925148
ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	243 mm
Package Level 1 Gross Weight:	0.004 kg
Package Level 1 EAN:	3472599102194
Package Level 2 Units:	14000 piece
Product Packing Type:	Bag
Package Level 1 Units:	20 piece

