

General Information

Extended Product Type:	JB6-50
Product ID:	1SNK906350R0000
EAN:	3472599097667
Catalog Description:	JB6-50 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	297 mm
Product Net Length:	26.8 mm
Product Net Depth:	26.8 mm
Product Net Weight:	38.1 g
Product Net Width:	6 mm

Technical

Spacing:	6 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 41 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1.3 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK4-22 ZDS4-22-R1 ZK2.5-SF ZK2.5-SF-R ZK2.5-S-R1 ZK4 ZK4-3P ZK4-4P ZK4-PE ZK4-PE-3P ZK4-PE-4P ZS4-PE-R2 ZS4-R2 ZS4-T3-R1 ZS6 ZS6-3S ZS6-3S-PE ZS6-4S ZS6-4S-PE ZS6-D1 ZS6-D1-PE ZS6-D2 ZS6-D2-PE ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage	Main Circuit 600 V

UL/CSA:

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

ATEX Certificate: 1SND162004A1706

CB Certificate: 1SND161025A0203

Data Sheet, Technical Information: 1SNK160029D0201

RoHS Information: 1SND230499F0202

Classifications

E-nummer: 2925377

ETIM 4: EC000489 - Cross-connector for terminal block

ETIM 5: EC000489 - Cross-connector for terminal block

ETIM 6: EC000489 - Cross-connector for terminal block

Object Classification Code: X

Container Information

Package Level 1 Width: 50 mm

Package Level 1 Length: 311 mm

Package Level 1 Height: 50 mm

Package Level 1 Gross Weight: 0.381 kg

Package Level 1 EAN: 3472599097667

Package Level 2 Units: 150 piece

Package Level 3 Units: 7200 piece

Package Level 1 Units: 10 piece

