

General Information

| | |
|------------------------|---|
| Extended Product Type: | SHB |
| Product ID: | 1SNK900602R0000 |
| EAN: | 3472599097384 |
| Catalog Description: | SHB Shield Connector |
| Long Description: | - Ensure the continuity of your shield connection, - Various connection solutions available: RILS cable ties, soldering, quick-connect. |

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Shield Connectors

Ordering

| | |
|-------------------------|----------|
| Minimum Order Quantity: | 20 piece |
| Customs Tariff Number: | 74199990 |

Dimensions

| | |
|---------------------|---------|
| Product Net Height: | 128 mm |
| Product Net Length: | 10.9 mm |
| Product Net Depth: | 10.9 mm |
| Product Net Weight: | 4.9 g |

Technical

| | |
|----------------------------------|--|
| Function: | Shield Connectors |
| Rated Voltage (U _r): | 320 V |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material: | Brass |
| Suitable For: | ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZS4-D1 ZS4-D2 ZS4-D2-S ZS4-D2-S-T ZS4-D-CH ZS6-D1 ZS6-D2 |

Environmental

| | |
|---|---|
| Resistance to Vibrations acc. to IEC 60068-2-6: | Compliant |
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
| Ambient Air Temperature: | Operation -55 ... +110 °C Storage -55 ... +110 °C |

Certificates and Declarations (Document Number)

| | |
|------------------------------------|-----------------|
| Instructions and Manuals: | 1SNK160027C0201 |
| ATEX Certificate: | 1SND162004A1706 |
| Data Sheet, Technical Information: | 1SNK160025D0201 |
| RoHS Information: | 1SND230502F0203 |

Classifications

| | |
|-----------------------------|------------------------------------|
| E-nummer: | 2925161 |
| ETIM 4: | EC002020 - Shield connection clamp |
| ETIM 5: | EC002020 - Shield connection clamp |
| ETIM 6: | EC002020 - Shield connection clamp |
| Object Classification Code: | X |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 158 mm |
| Package Level 1 Length: | 243 mm |
| Package Level 1 Gross Weight: | 0.098 kg |
| Package Level 1 EAN: | 3472599097384 |

Package Level 2 Units: 500 piece

Product Packing Type: Bag

Package Level 1 Units: 20 piece

