

General Information

Extended Product Type:	PS1-5-1-100
Product ID:	1SAM201916R1115
EAN:	4013614400667
Catalog Description:	PS1-5-1-100 Busbar
Long Description:	PS1-5-1-100 3-phase busbar for 5 MS116 /MS132 with 1 HK/SK, I _e =100A

Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010
EAN:	4013614400667

Container Information

Package Level 1 Length:	258 mm
Package Level 1 Height:	46 mm
Package Level 1 Gross Weight:	1.777 kg
Package Level 1 EAN:	4013614488283
Package Level 1 Units:	10 piece
Package Level 1 Width:	80 mm

Dimensions

Product Net Height:	38.8 mm
Product Net Depth:	13 mm
Product Net Weight:	0.172 kg
Product Net Width:	257.5 mm

Technical

Rated Operational Current (I _e):	100 A
Degree of Protection:	IP20
Standards:	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
Product Name:	Busbar
Suitable For:	MS116 MS132
Suitable for Product Class:	Manual Motor Starter
Rated Operational Voltage:	690 V

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -25 +70 °C Storage -50 ...+80 °C

Technical UL/CSA

Ampere Rating UL/CSA:	92 A
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V

Certificates and Declarations (Document Number)

Instructions and Manuals:	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
cUL Certificate:	1SAA963001-1701
Data Sheet, Technical Information:	1SBC100192C02-
Declaration of Conformity - CE:	1SAD938510-0056
GOST Certificate:	1SAA937000-2703
RoHS Information:	1SAA963003-4402
UL Certificate:	1SAA963001-1602

Classifications

E-nummer:	3112080
ETIM 4:	EC002498 - Accessories for low-voltage switch technology
ETIM 5:	EC002498 - Accessories for low-voltage switch technology
ETIM 6:	EC002498 - Accessories for low-voltage switch technology
eClass:	7.0 27379201
UNSPSC:	39121100
Object Classification Code:	W

