

## General Information

Extended Product Type:	232RU4
Product ID:	2CMA193241R1000
EAN:	7392696932417
Catalog Description:	Socket-outlet, panel mounting, 4h, 32A, IP44, unified flange, straight, 2P+E
Long Description:	Socket-outlet, panel mounting, earthing sleeve position 4h, rated current 32A, IP44 splashproof, unified flange, straight, 2-poles+earth, frequency 50-60 Hz, color code Yellow

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets for Panel Mounting

## Ordering

EAN:	7392696932417
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	93 mm
Product Net Height:	75 mm
Product Net Length:	104 mm
Product Net Depth:	104 mm
Product Net Weight:	0.24 kg

## Container Information

Package Level 1 Width:	143 mm
Package Level 1 Length:	397 mm
Package Level 1 Height:	187 mm
Package Level 1 Gross Weight:	0.24 kg
Package Level 1 EAN:	7392696932417
Package Level 1 Units:	10 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Cable Cross-Section:	2.5 ... 10 mm <sup>2</sup>
Color:	Yellow
Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Socket outlet, panel mounting, unified flange, straight
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232RU4
Mounting Type:	unified flange, straight
Number of Poles:	2
Object Classification Code:	2CMT005069
Product Main Type:	ERU
Product Name:	Industrial Socket Outlet Panel Mounting
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	32 A
Rated Voltage (U <sub>r</sub> ):	100 ... 130 V 100 ⚡ 130 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Socket Outlets for Panel Mounting

Suitable for Product Class: Industrial Plugs and Sockets

### Classifications

E-nummer: 2416653

UNSPSC: 39120000

