

### General Information

Extended Product Type:	216MVS4W
Product ID:	2CMA167823R1000
EAN:	7392696678230
Catalog Description:	Switched interlocked socket-outlet, 4h, 16A, IP67, 2P+E
Long Description:	Switched Interlocked Socket Outlet, vertical, earthing sleeve position 4h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Yellow

### Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Vertical

### Ordering

EAN:	7392696678230
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

### Dimensions

Product Net Width:	120 mm
Product Net Height:	253 mm
Product Net Length:	149 mm
Product Net Depth:	253 mm
Product Net Weight:	0.93 kg

### Container Information

Package Level 1 Width:	124 mm
Package Level 1 Length:	337 mm
Package Level 1 Height:	153 mm
Package Level 1 Gross Weight:	1.04 kg
Package Level 1 EAN:	7392696678230
Package Level 1 Units:	1 piece

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

### Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm
Cable Cross-Section:	1.5 ... 4 mm <sup>2</sup>
Cable Entry Position:	Top
Cable Outlets Per Side:	1xØ25
Color:	Yellow
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz
Function:	Switched interlocked socket outlet, vertical
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216MVS4W
Mounting Type:	Vertical
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	MVS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	100 ⚡ 130 V 100 ... 130 V

<b>RoHS Date:</b>	L23
<b>Standards:</b>	IEC 60 309-1, -2, -4
<b>Suitable For:</b>	Switched Interlocked Socket Outlets, Vertical
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

**Classifications**

<b>E-nummer:</b>	2416916
<b>UNSPSC:</b>	39120000

