

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0483920003

Status:

Active

Overview:

Consumer USB Products

Description:

Universal Serial Bus (USB 3.0) Reverse I/O Receptacle, Right-Angle, Type A, High-Temperature Blue Nylon, 15µ' Gold (Au) Plating, Contact Height 4.06mm

|                               |                                                            |
|-------------------------------|------------------------------------------------------------|
| Documents:                    |                                                            |
| <a href="#">3D Model</a>      | <a href="#">Packaging Specification PK-48392-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>       |

|                                |                                |
|--------------------------------|--------------------------------|
| General                        |                                |
| Product Family                 | I/O Connectors                 |
| Series                         | 48392                          |
| Application                    | Wire-to-Board                  |
| Component Type                 | Receptacle                     |
| Overview                       | Consumer USB Products          |
| Product Name                   | USB 3.0                        |
| Type                           | A                              |
| UPC                            | 887191452937                   |
| Physical                       |                                |
| Circuits (Loaded)              | 9                              |
| Color - Resin                  | Blue                           |
| Durability (mating cycles max) | 5000                           |
| Gender                         | Female                         |
| Keying to Mating Part          | Yes                            |
| Lock to Mating Part            | No                             |
| Material - Metal               | Copper Alloy                   |
| Material - Plating Mating      | Nickel, Tin                    |
| Material - Plating Termination | Gold                           |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.840/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Right Angle                    |
| PC Tail Length                 | 1.10mm                         |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| Packaging Type                 | Embossed Tape on Reel          |
| Panel Mount                    | No                             |
| Pitch - Mating Interface       | 2.00mm, 2.50mm                 |
| Pitch - Termination Interface  | 2.00mm, 2.50mm                 |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Ports                          | 1                              |
| Temperature Range - Operating  | -20°C to +85°C                 |
| Termination Interface: Style   | Through Hole                   |
| Electrical                     |                                |
| Current - Maximum per Contact  | 1.8A                           |
| Grounding to Panel             | Yes                            |
| Voltage - Maximum              | 30V AC/DC                      |
| Material Info                  |                                |
| Old Part Number                | 49392-0003                     |
| Reference - Drawing Numbers    |                                |
| Packaging Specification        | PK-48392-001                   |
| Sales Drawing                  | SD-48392-001                   |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

48392 Series

Mates With

USB 3.0 Type A Plug

This document was generated on 07/18/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**