

General Information

Extended Product Type:	232MHS6
Product ID:	2CMA167669R1000
EAN:	7392696676694
Catalog Description:	Switched interlocked socket-outlet, 6h, 32A, IP44, 2P+E
Long Description:	Switched Interlocked Socket Outlet, horisontal, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Horisontal

Ordering

EAN:	7392696676694
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	168 mm
Product Net Height:	129 mm
Product Net Length:	126 mm
Product Net Depth:	129 mm
Product Net Weight:	0.68 kg

Container Information

Package Level 1 Width:	144 mm
Package Level 1 Length:	202 mm
Package Level 1 Height:	140 mm
Package Level 1 Gross Weight:	0.75 kg
Package Level 1 EAN:	7392696676694
Package Level 1 Units:	1 piece


Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm/M25
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top and bottom
Cable Outlets Per Side:	1xØ25
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Switched interlocked socket outlet, horisontal
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232MHS6
Mounting Type:	Horisontal
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	MHS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	200 ... 250 V 200  250 V

RoHS Date:	L23
Standards:	IEC 60 309-1, -2, -4
Suitable For:	Switched Interlocked Socket Outlets, Horizontal
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416846
UNSPSC:	39120000

