

### General Information

Extended Product Type:	CP1-10G-20
Product ID:	1SFA619100R1022
EAN:	7320500240793
Catalog Description:	PUSHBUTTON#CP1-10G-20
Long Description:	Compact Pushbutton - Momentary - Flush - Green - Non-illuminated - Black plastic - 2NO

### Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Pilot Devices - Compact Range

### Ordering

EAN:	7320500240793
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

### Dimensions

Product Net Width:	0.030 m
Product Net Height:	0.030 m
Product Net Depth:	0.055 m
Product Net Weight:	0.022 kg

### Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	0.1 m
Package Level 1 Height:	0.03 m
Package Level 1 Length:	0.1 m
Package Level 1 Gross Weight:	0.022 kg
Package Level 2 Units:	10

### Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

### Additional Information

Actuator Type:	Flush
Bezel Material:	Black plastic
Block:	2NO
Color:	Green
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Function:	Momentary
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Non-illuminated
Mechanical Durability:	0.5 million
Number of Auxiliary Contacts NO:	2
Product Main Type:	CP1
Product Name:	Pushbutton
Product Range:	Compact
Product Type:	CP
Rated Frequency (f):	Supply Circuit 50 Hz Supply Circuit 60 Hz
Rated Operational Current AC-15 (I <sub>e</sub> ):	(220 / 240 V) 1 A (24 / 127 V) 1.5 A
Rated Operational Current DC-13 (I <sub>e</sub> ):	(125 V) 0.2 A (24 V) 0.3 A
RoHS Date:	0626 5

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SFC151003C0201
Declaration of Conformity - CE:	1SFA1-70
RoHS Information:	1SFC151012D0202

### Classifications

**E-number:** 3711270

**ETIM 4:** EC002024 - Accessories for control circuit devices

**ETIM 5:** EC002024 - Accessories for control circuit devices

**Object Classification Code:** S

**UNSPSC:** 39121512

---

