

General Information

Extended Product Type:	216RPR6
Product ID:	2CMA168261R1000
EAN:	7392696682619
Catalog Description:	Socket-outlet with RCD, 6h, 30mA, 16A, IP44, 2P+E
Long Description:	Socket-outlet with RCD, earthing sleeve position 6h, 30mA, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets with RCD

Ordering

EAN:	7392696682619
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	120 mm
Product Net Height:	243 mm
Product Net Length:	149 mm
Product Net Depth:	243 mm
Product Net Weight:	1.2 kg

Container Information

Package Level 1 Width:	124 mm
Package Level 1 Length:	337 mm
Package Level 1 Height:	153 mm
Package Level 1 Gross Weight:	1.2 kg
Package Level 1 EAN:	7392696682619
Package Level 1 Units:	1 piece

Environmental


RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, knock-outs 2xØ25mm
Cable Cross-Section:	1.5 ... 4 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	2xØ25
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Surface socket outlet with RCD, 30 mA
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216RPR6
Number of Poles:	3
Number of RCD 30mA:	1
Number of RCDs:	1
Object Classification Code:	2CMT005069
Product Main Type:	RPR
Product Name:	Industrial Socket Outlet with Protection
Protection Type:	Splashproof
Rated Current (I _n):	16 A
Rated Residual Current:	30mA

Rated Voltage (U_r):	200 ... 250 V 200  250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Socket Outlets with RCD
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-number:	2466300
UNSPSC:	39120000

