

Meaco 10L Small Home Dehumidifier



The Meaco 10L Small Home Dehumidifier is a small dehumidifier that is suitable for use in flats, apartments and up to a small three bedroom house. It has an electronic control panel which provides humidistat control of its drying performance and a laundry mode for drying washing.

The Meaco 10L features an energy conservation feature whereby it turns itself off when the desired relative humidity has been reached and then automatically turns back on when the relative humidity starts to rise again. This keeps both energy use and noise levels to an absolute minimum. The decibel rating of the Meaco 10L is very impressive, making it much more pleasant to live with than most other entry level dehumidifiers.

The low noise level is due in part to the use of a highly efficient rotary compressor as well as its well thought out design lines and carefully engineered air outlet that reduces wind noise.

The Meaco 10L is well loved by customers achieving an average rating of over 9 out of 10 on the Meaco website from reviewers, with many people commenting on how easy it is to live with and their surprise at how much water it takes out of the air and how quickly it dries a space out.

The Meaco 10L was the first dehumidifier to carry the Meaco name, it set the standard for the quality of dehumidifiers that Meaco produces and continues to lead the way to this day.

- ✓ 10 litres capacity at 30°C and 80%rh
- ✓ Neat, stylish design
- ✓ Dust filter
- ✓ Energy saving humidistat control
- ✓ Continuous drainage
- ✓ Simple Meaco style control panel
- ✓ Stops when tank is full
- ✓ Very Quiet for 10Ls - 43dBA
- ✓ Light and easy to carry



“The Meaco 10L is very robust and reliable. It’s definitely reduced the amount of heating oil being used and the time that the boiler is running. Keeps the air nice and dry and my allergy problems from dust mites have been alleviated too which is great. I’d certainly buy another one and am more than happy to recommend it for a small house.”

Customer quote taken from the Meaco website



“The Meaco 10L was the first dehumidifier that was good enough to carry the Meaco brand. The 10 litre dehumidifier represents the entry level price point for domestic dehumidifiers and it is difficult to design a quality product and still make the end user price attractive. The temptation is to cut corners or to lower quality in order to meet the price, especially with a higher VAT rate. We were determined not to do this with the Meaco 10L and I am very proud that we maintained our high standards and yet still managed to bring to the market a dehumidifier that is so well designed and built and yet sells at a very competitive price. The Meaco 10L stands out in it's sector and deserves all of the praise that it gets in reviews.”

Chris Michael – Director and Co-Founder of Meaco (U.K.) Limited with over 20 years experience in dehumidification.

For more information on the full product range and for help in selecting the correct dehumidifier, call free call 0500 418458 and talk to one of our experts

Model	Meaco 10L small home dehumidifier
For homes up to	a small 3 bedroom home
Dehumidifying capacity	10 litres/day (at 30°C, 80%RH)
Humidistat	Yes, electronic
Electronic controls	Yes
Air Filter	Yes - dust filter
Fan Speeds	One
Air flow (nominal)	>88m ³ /h
Continuous drainage option	Yes
Timer	No
Water container capacity	2 litres
Sound pressure level	Maximum 46dBA
Operating range	5 – 35°C
Power supply	220-240V/50Hz
Power consumption	220 Watts
Current (nominal)	1.0 A
Compressor type	Rotary
Refrigerant type / charge	R134a/120g
Automatic defrost	Yes
Dimensions (w x d x h)	296 x 186 x 483 mm
Net weight	8.75kg
Gross weight	9.52kg

Air treatment solutions since 1991

Meaco (U.K.) Limited

Meaco House
Parklands
Railton Road
Guildford
Surrey GU2 9JX

you dream...
...we supply

Telephone 01483 234900

Fax 01483 232700

Email sales@meaco.com

www.meaco.com