

Heavy Duty Knockdown Steel 2-Post Rack *DNRRHDKB*

Series

1,200 lbs Weight Capacity



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

Features

- Weighing in at just over 75 lbs., the DNRR Heavy Duty Knockdown Series boasts a 10-Gauge steel frame which is the thickest steel rack on the market.
- The knockdown self-squaring design takes just minutes to assemble.
- Our automated tapping assembly provides EIA-310-D compliant tapped rails on both the front and back to ensure flexibility when mounting equipment.
- When connecting multiple racks together, Hammond provided a 1.25" cable pass-thru. In addition we added numerous tapped and non-tapped holes for mounting power distribution, cable management and other accessories.
- Includes two (2) pairs of integrated 10-32 ground studs, spaced 5/8" apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair is located near the top of the rack, while the other at lower side.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on it's way we cover the rails and base with a thick layer of cardboard to prevent any damage that may occur during transportation.
- Tested to nearly double the suggested load rating of 1,200 lbs (544 kg).
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Universal Rack Shelf
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Outlet Strips
- 10-32 Mounting Hardware
- Grounding
- Rack Panels
- Two Post Mounting Clamping Shelf
- Two Post Centered Shelf
- Adjustable Depth DIN Rail Panel
- Hinged Acrylic Door Panel Cover
- Cable Management
- Rack Unit Label
- Rack and Cabinet Baying/Ganging/Joining Kit

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
DNRR63HDKB	69.13	20.00	15.00	36U	63.00	19.00
DNRR70HDKB	76.13	20.00	15.00	40U	70.00	19.00
DNRR77HDKB	83.13	20.00	15.00	44U	77.00	19.00
DNRR84HDKB	90.13	20.00	15.00	48U	84.00	19.00

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack** *Data subject to change without notice*

© 2016. Hammond Manufacturing Ltd. All rights reserved.