




















Assembly parts

Assembly parts

For the attachment of	Description	Dimensions	Model No.	Packs of
Front panels to unit side panels	Oval csk-screw ISO 7047-4.8-Z-A2F	M3 x 8 	3606.550	100
Rear panels to box-type plug-in units	Panhead posidrive screw ISO 7045-4.8-Z-A2F	M3 x 8 	3606.560	100
PCB holders (plastic) to front panels, top	Oval csk-screw ISO 7047-4.8-Z-A2F	M2.5 x 10 	3606.610	100
– Horizontal rails to side panels – Divider panels to horizontal rails – Horizontal rails to vertical supports	Panhead self-locking screw similar to DIN ISO 7045-8.8-Z-A2F	M4 x 12 	3654.300	100
– PCBs to PCB holders (die-cast for 3 U, 6 U), top – PCBs to extractor handles with 6 U	Panhead screw ISO 7045-4.8-Z-A2F	M2.5 x 8 	3654.320	100
– PCB holder (plastic) to type V/VI handles, bottom – PCBs to PCB holders (plastic) – Backplanes to tapped strips	Panhead screw ISO 7045-4.8-Z-A2F	M2.5 x 10 	3654.330	100
– Connectors to Z rails – Z rails to horizontal rails – Type V/VI handles to partial front panels, bottom right for ≥ 5 HP – Aluminium guide rails to horizontal rails – Mezzanine front panels	Panhead screw ISO 7045-4.8-Z-A2F	M2.5 x 6 	3654.340	100
Aluminium guide rails to horizontal rails (fastening of square nuts)	Retaining cage	M2.5	9901.417	100
Handle type V (plastic) to front panels and box type plug-in units	Mounting kit for type V handle (plastic): Cover black Cover grey Hex nut Screw Screw Square nut DIN 502-11H-A2F	M2.5 M2.5 x 16 M2.5 x 12 M2.5	3687.519	1 set
Connectors to PCBs	Panhead screw ISO 7045-4.8-Z-A2F	M2.5 x 12 	3654.350	100
Guide rails (plastic) to horizontal rails	Screw for plastic WN 1413	M2.2 x 6 	3654.360	100
– Flat front panels to handles type V, VI – Aluminium guide rails to horizontal rails	Square nut DIN 562-A2F	M2.5 	3654.370	100
– Flat front panels to horizontal rails – Trim frame to conceal the front sections of the horizontal mounting kit	Captive screws (cheese-head) and plastic collars	M2.5 x 11 	3658.160	100 set
Flat front panels	Plastic collars		3687.021	100
PCB to type III handle	Screw for plastic WN 1412	M3.0 x 8 	3658.190	100
– PCBs to PCB holders (plastic) – PCB holders to front panels, top	Hex nut ISO 4032-8	M2.5 	3658.210	100
– Backplanes to threaded inserts – Air partitions to horizontal rails	Mounting kit for backplanes: Panhead screw ISO 7045-4.8-Z-A2F Washer PE, natural DIN 125	M2.5 x 6  2.7 	3684.019	100
– Covers to mounting blocks – EMC contact profiles	Flat csk-screw ISO 7046-1-4.8-Z-A2F	M3 x 6 	3684.233	100
Covers to side panels	Mounting block		3684.234	10
Type V/VI handle to front panels	Bracket		3684.435	100
Female connector to PCB attachment	Pop rivet DIN 7340-B-CuZn	2.5 x 0.3 x 10	3684.482	100
Ground contact to keyable guide rails	Fastening screw for ground contact	M3.5 x 12	3684.109	50