






















Assembly parts

For the attachment of	Description	Dimensions	Model No.	Packs of
Fans to fan mounting plate	Mounting kit for fans: Flat csk-screw ISO 7046-1-4.8-Z-A2F Hex nut ISO 4032-8 Serrated washer DIN 6797-A-Fst	M4 x 12  M4  4.3 	3685.197	1 set
Covers to side panels	Mounting kit for covers: Mounting block Flat csk-screw ISO 7046-1-4.8-Z-A2F	 M3 x 6 	3685.256	24 sets
PCB holders (die-cast) to front panels, top	Oval csk-screw ISO 7047-4.8-Z-A2F	M2.5 x 8 	3685.282	100
– Covers/box type plug-in units type I/II – Contact/spring sections for 3-part front panels	Flat csk-screw ISO 7046-1-4.8-Z-A2F	M2.5 x 5 	3685.289	100
– Handles on front panels for box type plug-in units – Front panels to hinge strip	Flat csk-screw ISO 7046-1-4.8-Z-A2F	M2.5 x 6 	3685.290	100
Holder (horizontal assembly kit) to horizontal rail	Flat csk-screw similar to ISO 7046-1-4.8-Z-A2F	M2.5 x 5 	3686.916	100
Holder (horizontal assembly kit) to horizontal rail	Flat csk-screw similar to ISO 7046-1-4.8-Z-A2F	M2.5 x 8 	3686.917	100
Contact and spring sections on 3-part front panels without countersink	Panhead csk-screw ISO 7046-4.8-Z-A2F	M2.5 x 5 	3686.924	100
Recessed flanges to side panels	Mounting kit for recessed flanges: Panhead self-locking screw similar to DIN ISO 7045-8.8-Z-A2F Hex nut ISO 4032-8 Washer	M4 x 8  M4  4.3 	3687.015	4 sets
Fastening the threaded inserts in horizontal rails	Grub screw ISO 7434-14H	M2.5 x 8 	3687.020	100
– EMC front panels to horizontal rails – EMC trim frame to conceal the front sections of the horizontal mounting kit	Centering screw with slotted head	M2.5 x 11 	3687.050	100
EMC front panels to horizontal rails	Centering screw posidrive	M2.5 x 11 	3687.051	100
Front panels and rear panels to horizontal rails	Collar screw, cheese-hed slotted	M2.5 x 11 	3685.097	100
Type V/VI handles (aluminium) to front panels	Mounting kit for type V/VI handles: Panhead screw ISO 7045-1-4.8-Z-A2F Bracket Square nut DIN 562-11H-A2F	M2.5 x 6   M2.5 	3687.146	1 set