

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510670900](#)
Status: **Active**
Description: 3.50mm Pitch Wire-to-Wire and Wire-to-Board Housing, Positive Lock, 9 Circuits

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-51067-007 (PDF) |
| Drawing (PDF) | Product Specification PS-51067-008 (PDF) |
| Product Specification PS-51067-001-001 (PDF) | Product Specification PS-51067-016 (PDF) |
| Product Specification PS-51067-002-001 (PDF) | Product Specification PS-51067-017 (PDF) |
| Product Specification PS-51067-003 (PDF) | Product Specification PS-51067-018 (PDF) |
| Product Specification PS-51067-004 (PDF) | Product Specification PS-51067-019-001 (PDF) |
| Product Specification PS-51067-005 (PDF) | Product Specification PS-51067-022-001 (PDF) |
| Product Specification PS-51067-006 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|------------------------------------|
| Product Family | Crimp Housings |
| Series | 51067 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Product Name | N/A |
| UPC | 800754363501 |


Physical

| | |
|-------------------------------|-----------------|
| Circuits (maximum) | 9 |
| Color - Resin | Natural |
| Flammability | 94V-0 |
| Gender | Female |
| Glow-Wire Compliant | No |
| Material - Resin | Polyester |
| Net Weight | 1772.800/mg |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.50mm |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|--|
| Product Specification | PS-51067-001-001, PS-51067-002-001, PS-51067-003, PS-51067-004, PS-51067-005, PS-51067-006, PS-51067-007, PS-51067-008, PS-51067-016, PS-51067-017, PS-51067-018, PS-51067-019-001, PS-51067-022-001 |
| Sales Drawing | SD-51067-**00 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

[51067](#) Series

Mates With

[51114](#) , [53258](#) , [53259](#) , [53265](#) , [53266](#)

Use With

[50217](#) Crimp Terminals