


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0471510002](#)
Status: **Active**
Overview: High Definition Multimedia Interface (HDMI)* Products
Description: 0.50mm Pitch HDMI* Receptacle, Right Angle with Screw Flange, Front Solder Tab Length 1.80mm, Mounted Height 16.08mm, Shell Nickel (Ni) Plated, without Back Cover, Black Housing, Tray Package, 19 Circuits, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-47151-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-47152-001-001 \(PDF\)](#)



General

Product Family	I/O Connectors
Series	47151
Application	Wire-to-Board
Component Type	Receptacle
Electrical Model	Yes
MolexKits	Yes
Overview	High Definition Multimedia Interface (HDMI)* Products
Product Name	HDMI*
Type	N/A
UPC	822350117081

Physical

Boot Color	N/A
Circuits (Loaded)	19
Color - Resin	Black
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Bismuth
Net Weight	2.481/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	With Flange
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	40V DC

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[47151 Series](#)

Mates With

[88768 HDMI* Cable Assembly, 88764 HDMI* Adapter, 88767 HDMI* Adapter](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	255

Material Info**Reference - Drawing Numbers**

Electrical Model Document	EE-47151-001, EE-47151-002
Packaging Specification	PK-47151-002
Product Specification	PS-47152-001-001
S-Parameter Model	SP-47151-002

* High Definition Multimedia Interface and HDMI are trademarks of HDMI Licensing, LLC.

This document was generated on 02/27/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION