

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002092116**
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-43660-9999-001 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Crimp Terminals |
| Series | <u>1380</u> |
| Application | Power |
| Crimp Quality Equipment | Yes |
| Overview | <u>Standard .093" Pin and Socket Connectors</u> |
| Packaging Alternative | <u>02-09-2118 (Loose)</u> |
| Product Name | Standard .093" |
| UPC | 800753760004 |

Physical

| | |
|--------------------------------|----------------------|
| Durability (mating cycles max) | 25 |
| Gender | Male |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.323/g |
| Packaging Type | Reel |
| Plating min - Mating | 0.508µm |
| Plating min - Termination | 0.508µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.52-3.05mm |
| Wire Size AWG | 18, 20, 22 |
| Wire Size mm ² | N/A |

Solder Process Data


| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 1380-(P901) |
|--------------------|-------------|

Reference - Drawing Numbers

| | |
|-----------------------|-----------------------------|
| Product Specification | PS-02-09, PS-43660-9999-001 |
| Sales Drawing | SD-1380-* |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1380 Series](#)

Use With

[1619](#) Plug or Receptacle Housing, [1545](#) Plug or Receptacle Housing, [1396](#) Plug or Receptacle Housing, [1490](#) Plug or Receptacle Housing, [2629](#) Plug or Receptacle Crimp Housings, [1261](#) Plug or Receptacle Housing, [1292](#) Plug or Recept