

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009524034

Status:


Active

Overview:

KK® Interconnect System - Molex

Description:

3.96mm Pitch KK® Crimp Housing, Female, Friction Ramp, 3 Circuits



Series image - Reference only

Documents:	
3D Model	Product Specification PS-5239-006 (PDF)
Drawing (PDF)	Product Specification PS-5239-007 (PDF)
Product Specification PS-5239-002 (PDF)	Product Specification PS-5239-010 (PDF)
Product Specification PS-5239-004-001 (PDF)	Product Specification PS-5239-011 (PDF)
Product Specification PS-5239-005-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5239
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753613942
Physical	
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	821.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	5239-03
Reference - Drawing Numbers	
Product Specification	PS-5239-002, PS-5239-004-001, PS-5239-005-001, PS-5239-006, PS-5239-007, PS-5239-010, PS-5239-011
Sales Drawing	SD-5239-N

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/01/2017 (12	
January 2017)	
Halogen-Free	
Status	
Low-Halogen	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5239 Series

Mates With

Right Angle PCB Header, 5274 5272 , Vertical PCB Header 5271 , 5273

Use With

5168 Cat Ear Crimp Terminals for 22-28 AWG, 5167 Cat Ear Crimp Terminals for 18-24 AWG, 2478 Crimp Terminal, 2578 Crimp Terminal