



LB130 Smart Wi-Fi LED Bulb

With Color-Changing Hue



LB130



No Hub
Required



Colors for
Every Occasion



Remote
Access



Scheduling



Kasa
App



Energy
Saving

Highlights

Colors for Every Occasion

With colors for every occasion and adjustable brightness, the LB130 offers even more lighting possibilities to suit your aesthetic, your environment and your mood for various occasions. You can go wild with your imagination!



Dimming Option

With adjustable brightness, the LB130 lets you customize your lighting to suit your mood at any time.



Highlights

Works with Any Wi-Fi Router

Save cost and easy setup with no extra hardware required.



Energy Saving

Reduce energy used by up to 80% without brightness or quality loss compared to a 60W incandescent bulb, and lasts up to 22.8* years.

*based on 3 hours/day, 11 cents/kWh; cost depends on rates and use



Features



Ease of Use

- **No Extra Hardware Required** – Convenient smart Wi-Fi bulb with no extra hardware required.
- **Anywhere and Anytime** – Easy setup and control from anywhere with the free Kasa app.
- **Schedule Your Light** – Set schedules to turn on/off the Smart Bulbs at any chosen time for your convenience.



Compatibility

- **Works with Amazon Alexa** – You can pair the Smart Wi-Fi LED Bulb with Amazon Echo, Dot, Tap and other supported devices for voice control.
- **Compatible with Android, iOS** – The free Kasa app lets you run them from any Android (4.1 and higher) or iOS (iOS 8 and higher) smartphone.



Rich Functionality

- **Scene Mode** – Save your light settings as different scenes to enjoy instant access to them. Smart Wi-Fi bulbs can be controlled individually or as a group.
- **Away Mode** – The smart Wi-Fi bulb can make it look like someone is home by turning on and off at different times.

Features



Lighting

- **Colors for every occasion** – Change the color and intensity as you wish, navigate the tunable white light from warm to cool until you feel comfortable.
- **Circadian mode** – Let you wake up refreshed and fall asleep calmly.
- **Durable Bulb** – Provide you stable and customized lighting for up to 22.8 years*

*Based on 3hrs/day

Specifications

Working Status

- **Typical Lumen Output:** 800lm
- **Input Power (Actual power draw in Watts):** 11W typical
- **Stand-by (Light off) power:** 0.5W Max
- **Color Temperature:** 2500K-9000K & RGB full color
- **Rated input Voltage:** 220-240V 50Hz
- **Beam Angle:** 180 Degree typical
- **Dimmable:** Yes (via app and cloud only)



General

- **Package Contents:** Smart Wi-Fi LED Bulb LB130, Quick Installation Guide
- **Bulb Lifetime (to 50% brightness level) :** 25000 Hrs min @Ta=25C
- **Lamp Base :** E27
- **Certifications:** EMC, Wi Fi, ROHS, CE
- **Operating Temperature:** - 15°C to + 40°C
- **Operating Humidity:** 85% RH NC min
- **Weight:** 180g

Network

- **Protocol:** IEEE 802.11b/g/n
- **Wireless Type:** 2.4GHz, 1T1R
- **System Requirements:** Android 4.1 or higher, iOS 8 or higher