
150-330 To 150-341



# TOSER CABLE CLIPS

# TOYER CABLE CLIPS

Hobust desig	n in tough plas	tic. Assembled with hard	lened steel, zinc plate	ed masonry pins	<u> </u>	
PACK CODE 10 Boxes of 10	NOMINAL 00 SIZE mm	CABLE		AVERAGE BOX QUANTITY	QUANTITY PER Y OUTER CARTO	CABLE SECTION N
PARALLEL T	WIN White only	1				77
7PT	5.0 x 2.0	Bell Wire		100		įį.
7PM	5.3 x 2.8	Twin Figure ∞	(CMA CODE 2812X)	100		
7SM	6.2 x 4.1	Sheathed Twin 0.5mm <sup>2</sup>	(CMA CODE 3192Y)	100		
	Grey and White					Ŋ
72C	7.4 x 4.2	Flat Twin 1.0mm <sup>2</sup>	(CMA CODE 6192Y)	100	20,000	
FLAT TWIN &	EARTH Grey o	or White				SINGLE
7KF 1.0	8.0 x 4.4	1.0mm <sup>2</sup>	(CMA CODE 6242Y)	100	20,000	7
7KF 1.5	8.3 x 4.6	1.5mm <sup>2</sup>		100	20,000	
7KF 2.5	9.7 x 5.4	2.5mm <sup>2</sup>		100	20,000	11
7KF 4.0	12.0 x 6.5	4.0mm <sup>2</sup>		100	20,000	
7KF 6.0	13.8 x 7.3	6.0mm <sup>2</sup>		100	20,000	
7KF 10.0	17.4 x 8.8	10.0mm <sup>2</sup>		100	10,000	لہا ال
7KF 16.0	20.3 x 10.1	16.0mm <sup>2</sup>		50	5,000	· · · · · · · · · · · · · · · · · · ·
7DKF 1.0	15.4 x 4.4	1.0mm <sup>2</sup>	(CMA CODE 6242Y)			DOUBLE
7DKF 1.5	16.6 x 4.6	1.5mm <sup>2</sup>		100		N
7DKF 2.5	19.4 x 5.4	2.5mm <sup>2</sup>		100		
73C&E	E & EARTH Gre 10.5 x 4.4	1.0 & 1.5mm <sup>2</sup>	(CMA CODE 6243Y)	100		
OUND White o						Ţ
7RC2 <sup>3</sup> / <sub>4</sub>	2.75			100		- 11
7RC31/2	3.5			100		
7RC4	4.0			100		
7RC5	5.0			100	7400	
7RC6	6.0			100		(( ))
7RC7	7.0	Round - Circular		100		لىك قىلى
7RC8	8.0			100		▼
8RC9	9.0			100		
7RC10	10.00			100		
7RC11	11.0			100		
7RC12	12.0			100		
7RC14	14.00			50		
7RC16	16.0			50		
PIN PLUG			y - y - we did not			
7PP		CABLE CLIPS WHEN D HARD EVEN FOR SONRY PINS				

## THE PROFESSIONAL'S CHOICE!

TOWER PLASTIC CABLE CLIPS are designed and manufactured from high quality materials. The tough plastic material has been specially selected to suit the requirement according to application, style and size of clip.

The hardened steel pins, are pre-assembled into the clips for maximum utility, being made from a high carbon steel — critically heat-treated, then bright zinc electroplated.

For small bell-wire type cables the PT, PM and SM clips cover most requirements.

The 'FLAT' clip range originated by TOWER for the

CMA TWIN & EARTH cables, have virtually become 'standard' with the trade.

For ROUND cables, TOWER clips are available to accommodate a wide series of cable diameters.


ALL TOWER plastic clips with pre-assembled hardened and plated steel nails provide a professional and low cost fixing.

- FUNCTIONAL AND NEAT DESIGN
- HIGH QUALITY
- FAST FIXING LOW IN-PLACE-COSTS
- THE PROFESSIONALS CHOICE

#### M.I. CABLE CLIPS For use with Mineral Insulated Cables

CODE No	. CABLE		SECTION	
	Bare	PVC Covered		
7M16	2L1, 2L1.5, 3L1, 3L1.5, 4L1		ROUND	Τſ
7M17	2L2.5, 4L1.5	2L1, 2L1.5, 3L1	Orange	
7M18	2L4, 7L1	2L2.5, 3L1.5, 4L1		
7M19	7L1.5	2L4, 4L1.5, 7L1, 7L1.5		
TR CABL	E CLIPS For use with Coaxial	Cables		
TRC5	Round—Circular Nomir	nal Size 5.0mm	ROUND	Ţ
TRC6		6.0mm	Brown	
11100		0.0111111		

### **TOWER SINGLE BLOW**



The Tower Single Blow Clip design is a simple one piece operation giving a labour cost saving and a quick easy method of installation into metal, concrete and brickwork for fixing both cable and pipe.

Tower Single Blow Clips are recommended for the installation of central heating pipes by the one operation thus avoiding the use of a clip, screw and plug giving labour cost saving.

The range of clips are supplied to cover diameters from 6mm to 18mm.

#### **TOWER SINGLE BLOW CLIPS White or Black**

CODEN	D. NORMAL DIAMETER	PER PACK OF 100
72U1	Round 6–8mm	6.50
72U2	Round 9–13mm	6.50
72U3	Round 14–18mm	6.50

#### TOWER SINGLE BLOW FLAT CABLE CLIPS White or Grey

CODE No.	NORMAL DIAMETER		PER PACK OF 100	
72U4	Flat Twin & Earth	2.5mm <sup>2</sup>	6.50	_