

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348268124](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Right Angle Header, Dual Row, 12 Circuit, Polarization Option A, Black, Tape and Reel

Documents:

Drawing (PDF)	Packaging Specification PK-47799-0001 (PDF)
Product Specification PS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-31301-786 (PDF)	Product Literature (PDF)

General

Product Family	PCB Headers
Series	34826
Application	Power, Signal, Wire-to-Board
Overview	Mini50™ Connection Systems
Product Literature Order No	987650-5442
Product Name	Mini50™
UPC	191128064118

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	2.414/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole


Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-31301-786, PK-47799-0001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34826-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[34826](#) Series

Mates With

[34824](#) Mini50™ Unsealed Dual Row Receptacle

This document was generated on 04/13/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION